

# FORNEY TEST MACHINES

F-450-VFD AUTOMATIC COMPRESSION TEST MACHINE

## COMPRESSION MACHINE

<b>LOAD CAPACITY</b>	<b>FRAME</b>	<b>CONTROL SYSTEM</b>
450,000lb	Standard (F)	VFD
<b>TEST TYPES</b>	<b>TESTING MATERIALS</b>	<b>DESIGNED &amp; BUILT BY FORNEY</b>
Compression, Flexural, Modulus of Elasticity/Poisson's Ratio (MP), Proppant Crush Resistance, Tensile Splitting	Cylinders, Cubes, Grout Prism, Beams, Proppant Sand, Rock Core	Exceeds ACI Recommendations



[DOWNLOAD SPEC SHEET](#)

[GET A QUOTE](#)

## GET A CONNECTED MACHINE AND SAVE \$1,500

### NATIVE TWO-WAY INTEGRATION WITH CMT SOFTWARE

Connected Testing Machines allow technicians to get more done faster with minimal human error through a two-way integration with ForneyVault. Resulting in 99.9%+ fewer manual errors, 66%+ increase in productivity, and 100% unalterable, unquestionable data.

- ▲ "One-touch" test starts and automatic controls
- ▲ Pre-test "Smart Checks" to validate test parameters
- ▲ Automatic preload calculations, notifications for individual and average low breaks and excessive variance, automatic data transfer, and more

[SEE HOW IT WORKS](#)

[GET A CONNECTED QUOTE](#)

CLICK TO CLOSE ADDITIONAL PRODUCT INFORMATION

## HARDWARE

### FRAME

Designed and built by Forney. These machines are ideal for the general lab because of their versatility. Standard Testing Machines have frames manufactured from solid steel into a one-piece, welded unit that exceeds ACI recommendations. All machines in the series have Lexan fragment guard doors for enhanced safety.

⋮ [Ask me anything...](#)



The load frame is manufactured from structural steel angles welded to top and bottom crossheads of solid steel plate. The hydraulic cylinder assembly is mounted to the bottom crosshead, with force being applied in upward direction and debris protection by metal shroud.

## MATERIALS

Test hydraulic cement, down hole cement, mortar, grout, concrete, self-consolidating concrete, CLSM, flowable fill, proppant, ceramics, metals, and plastics.

## HYDRAULIC

The hydraulic unit is supplied as a complete, fully integrated assembly. The unit is pre-piped and pre-wired. It incorporates hydraulic valves, including an optional proportional valve for controlled piston retract required by code for Modulus of Elasticity and Poisson's Ratio tests.

The human machine interface (HMI), hydraulic unit, E-Stop, and dump valve are directly connected to the compression unit. Single unit design permits easy installation and provides portability without disassembling of hydraulic or electrical components.

## ELECTRICAL

A PC-based system utilizes a variable frequency drive to control the hydraulic pump motor. This maximizes efficiency – only running the pump at speeds necessary to achieve the desired pressure. This energy-efficient approach dramatically reduces heat build-up in the hydraulic system and greatly extends hydraulic component life.

Here are the main components of the system:

- ▲ Variable frequency drive (VFD)
- ▲ Windows-based touchscreen human machine interface (HMI)
- ▲ Pressure transducer that provides pressure feedback
- ▲ E-stop PB
- ▲ Limit switch
- ▲ Solenoid-operated dump valve

## SAFETY FEATURES

Several safety features are incorporated to protect both operator and testing machine:

- ▲ Maximum Capacity Protection: A high-pressure safety relief valve protects the hydraulic circuit and load frame from exceeding maximum capacity.
- ▲ Overextension Protection: A piston over-extension limit switch system protects against piston extension beyond maximum travel.
- ▲ Fragment Safety Guard: Fragment guards with latches and hinges are mounted to both the front and rear of the compression frame. Fragment guards are made of Lexan® and permits clear viewing of the test in process.

## SOFTWARE

### EASY AUTOMATIC TESTING

push one button and the machine performs the complete test, including piston retract. Accurately controls the rate of load at the desired setting, thus no question about meeting ASTM (or other) specifications and ensuring repeatable results. Frees the operator to do other tasks while testing is in process.

### DIGITAL CONTROL SYSTEM

Setup of testing protocol, real-time display of test data, and post-test data transfer is accomplished through the ForneyLink touchscreen HMI. The operator can navigate options for:

- ▲ Test Run
- ▲ Test Setup



- ▲ Machine Setup
- ▲ Calibration
- ▲ Reporting and Data Transfer
- ▲ Diagnostics

Provides simultaneous display of force, stress, and rate of load and displays a real-time graph of Load vs. Time, or Stress vs. Strain. Standard functionality includes data collection by the ForneyLink HMI for printing and transfer. Data from optional extensometer and compressometer displacement transducers are also collected by the HMI. This data is captured with the same timestamp as the load data.

#### CMT SOFTWARE INTEGRATION

Connected testing machines natively integrate with ForneyVault CMT software, improving important processes before and after an automatic test.

Before the test, Connected machines will:

- ▲ Enable positive specimen identification via barcode scan
- ▲ Provide pre-test “Smart Checks” based on preloaded sample and specimen data to validate sample date, ample size and type, and expected strength.
- ▲ Validate specimen geometry.
- ▲ Calculate preload settings based on actual and/or expected strength.

After the test, Connected machines will:

- ▲ Provide a detailed XY plot data for every test performed.
- ▲ Transfer data automatically to LIMS packages, QC systems, or other software.
- ▲ Alert to warn calibration expiration.
- ▲ Notify correction factor use, individual low breaks, and excessive variance.
- ▲ Enable intelligent workflows for detailed reporting and approvals.

#### REMOTE SUPPORT

with a user-provided Internet connection (either Wi-Fi or Ethernet), all Forney VFD systems are capable of real-time, online support from the Forney Support Team for basic settings and test setup to advanced troubleshooting, fault finding, and software updates.

We offer unlimited Remote Technical Support for all Forney Testing Machines during the two-year warranty period.

For ForneyVault® subscribers, post-warranty remote technical support fees are waived for the life of your subscription.

Please refer any special requirements to a Forney sales representative.

**\* Specifications are subject to change without notice.**



ACCESSORIES	
<a href="#">Cylinder Compression (6" Dia x 12" L with Pad Caps) (150mm x 300mm)</a>	TA-0101 Cylinder Top Platen Assembly (included w/ machine)
<a href="#">Cylinder Compression (6" Dia x 12" L with Capping Compound or Ground Ends) (150mm x 300mm)</a>	TA-0103 Cylinder Top Platen Assembly
<a href="#">Cylinder Compression (4" Dia x 8" L with Pad Caps) (100mm x 200mm)</a>	TA-0101 Cylinder Top Platen Assembly (included w/ machine) TA-0202 Spherical Seat Extender, 4" H
<a href="#">Cylinder Compression (4" Dia x 8" L with Capping Compound or Ground Ends) (100mm x 200mm)</a>	TA-0103 Cylinder Top Platen Assembly TA-0202 Spherical Seat Extender, 4" H
<a href="#">Compressive Strength and Elastic Moduli of Intact Rock Core Specimens</a>	TAG-0090 2x4in Compressometer/Extensometer
<a href="#">Cylinder Tensile Splitting (6" Dia x 12" L) (150mm x 300mm)</a>	TAG-0023 Cylinder Splitting Kit
<a href="#">Cylinder Tensile Splitting (4" Dia x 8" L) (100mm x 200mm)</a>	TA-0107-01 Cylinder Splitting Accessory TM-0074 Bottom Platen TA-0171 Spacer, 2" H
<a href="#">Cube (2") (50mm)</a>	TAG-0056 Cube (2") Accessory Kit
<a href="#">Cube (6") (150mm)</a>	TA-0111 Cube Top Platen Assembly (2) TA-0202 Spherical Seat Extender, 4" H
<a href="#">Flexural Beam (6" x 6" x 18") (150mm x 150mm x 450mm)</a>	TA-0166 Flexural Testing Accessory
<a href="#">Grout Prism (3" x 3" x 6") (75mm x 75mm x 150mm)</a>	TA-0101 Cylinder Top Platen Assembly (included w/ machine) (2) TA-0202 Spherical Seat Extender, 4" H
<a href="#">MOE (6" diameter) (150mm)</a>	LA-0488-E6-SG Compressometer  *Must have compression accessories  *Must have -M or -MP machine
<a href="#">MOE (4" diameter) (100mm)</a>	LA-0488-E4-SG Compressometer  *Must have compression accessories  *Must have -M or -MP machine
<a href="#">MOE &amp; Poisson's Ratio (6" Diameter) (150mm)</a>	LA-0488-P6-SG Compressometer/Extensometer  *Must have compression accessories  *Must have -MP machine

FACTORY INSTALLED OPTIONS	
Voltage	110/220VAC Single Phase  The full load amperage for standard VFD Control Systems is less than 5A (115VAC single phase voltage). We recommend standard 15A or 20A circuits.
Displacement	Available Upgrade
Optional Test Protocol Capabilities	ASTM C469 MOE (M)  ASTM C469 MOE & Poisson's Ratio (MP)  ISO 13503-2 Proppant (SW-0010)  *Additional accessories required  *Inquire about other test type requirements
Capacity Options	Dual Range (2 transducers) on Single Frame (2R)
Frame Options	Second Frame Capability (AB)  Dual Frame Capability (adds 250k de-rated frame to machine) (2F)  Dual Frame Capability (adds 30k frame setup for Concrete Beam) (BT)
Travel Limit Switch	Standard Equipment

SPECIFICATIONS	
Load Capacity Range	4,500lbf - 450,000lbf
Vertical Opening	19.125"
Horizontal Opening	9.5"
Ram Diameter	8.5"
Piston Stroke	2.5"
Platen Hardness	60 HRC
Lower Platen Dimension	10.5" Diameter
Upper Platen Dimension	6.5" Diameter
Oil Reservoir Capacity	2 Gallons
Overall Width	34"
Overall Depth	24" <span style="float: right;">⋮</span>

<u>MOE &amp; Poisson's Ratio (4" Diameter), (100mm)</u>	<p>LA-0488-P4-SG Compressometer/Extensometer</p> <p>*Must have compression accessories</p> <p>*Must have -MP machine</p>
<u>MOE &amp; Poisson's Ratio (2" Diameter), (50mm)</u>	<p>TA-3542-03 Axial Extensometer 2"</p> <p>TA-3975-01 Diametral 0.030"</p> <p>*Must have compression accessories</p> <p>*Must have -MP machine</p>
<u>Proppant (2" diameter), (50mm)</u>	<p>TA-0119-11 Top Platen Assembly</p> <p>TA-0151 Bottom Platen</p> <p>TA-0174 Spacer, 6" H</p> <p>TM-2035 Centering Stud</p> <p>TA-0002 Proppant Crush Piston &amp; Cell</p>

Overall Height	60"
Unit Weight	1,480lbs
Test Standard Ready	<p>ASTM C39 Cylinders in Compression (6" diameter x 12" length, pad cap testing)</p> <p>ASTM E4</p>
Test Standard Capable	<p>ASTM C39, C78, C293, C109, C469, C496, C1019, D7012</p> <p>AASHTO T 22, T 97, T 106</p> <p>ISO 13503-2</p> <p>API RP 56</p> <p>BS 1610, BS 1881, EN ISO7500-1, EN 12390-3, EN 12390-4</p>

